
www: im-metalioining.com



## Argo-braze<sup>™</sup> 61V – Silver Brazing Filler Metal

Argo-braze<sup>™</sup> 61V is a silver-copper-indium brazing filler metal. It is manufactured only as a vacuum tube grade material with low and controlled levels of volatile impurities. The indium content of this filler metal reduces the alloy's melting temperature and gives it improved wetting on ferrous parent metals over the straight silver-copper filler metal Argo-braze<sup>™</sup> 72V.

Argo-braze<sup>™</sup> 61V is intended for use in fluxless atmosphere (reducing or inert gas) or vacuum brazing applications, however, it is prone to liquate (separate into low and high melting constituents) if it is heated slowly through its melting range. For this reason rapid heating methods should be employed wherever possible.

This filler metal is typically used for brazing vacuum tube type components and for the brazing of metalised ceramics in vacuum tube devices or in the production of ceramic to metal seals. Where ceramics are being brazed to a low expansion nickel alloy care should be taken (nickel plating / stress relieving) to prevent intergranular penetration (liquid metal stress cracking) of the nickel alloy.

Argo-braze<sup>™</sup> 61V can be used as the last stage in a multi-step, sequential brazing operation with high melting point filler metals like Argo-braze<sup>™</sup> 72V, Pallabraze<sup>™</sup> 810 etc.

This filler metal was formerly called IN15.

**Composition:** 61.5%Ag, 24%Cu, 14.5ln%

Conforms to: AWS A5.8 BVAg-29

Melting range: 630-705°C

## **Uses for This Product**

Argo-braze™ 61V is used for brazing components for vacuum tube devices and ceramic to metal seals.

## **Conditions for Use**

This product can be used to braze in hydrogen, an inert atmosphere or in a vacuum without the need for a flux. When vacuum brazing a partial pressure brazing technique should be used to prevent the vaporisation of the silver within the alloy.

## **Product Availability**

Telephone: +44 (0) 1763 253200

Special order only.

Johnson Matthey Plc cannot anticipate all conditions under which this information and our products or the products of other manufacturers in combination with our products will be used.
This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is given in good faith, being based on the latest information available to Johnson Matthey Plc and is, to the best of Johnson Matthey Plc ssumes no responsibility therefore and disclaims any liability for any loss, damage or injury howsoever arising (including in respect of any claim brought by any third party) incurred using this information. The product is supplied on the condition that the user accepts responsibility to satisfy himself as to the suitability and completeness of such information for his own particular use. Freedom from patent or any other proprietary rights of any third party must not be assumed. The text and images on this document are

This datasheet may only be reproduced as information, for use with or for resale of Johnson Matthey products. The JM logo©, Johnson Matthey© name and product names referred to in this document are trademarks of Johnson Matthey. Easy-flo® and Silver-flo® are registered to JM in the EU. Sil-fos™ is registered to JM in the UK and certain other countries but is marketed as Mattiphos™ in Germany and the USA.

