

Liquid Flux No 25



Easy-flo™ No. 25 Liquid Flux

Johnson Matthey Easy-flo™ No. 25 Liquid Flux is a liquid brazing flux suitable for use with silver brazing filler metals. It has a working range of 600-850°C and is suitable for use with filler metals melting below 800°C (such as Silver-flo™, Easy-flo™ and Argo-braze™ alloys). Easy-flo™ No. 25 Liquid Flux formerly sold as Liquid Flux No. 25.

Easy-flo™ No. 25 Liquid Flux can be used for jewellery parts or any other application that requires the use of a liquid flux or where limited fluxing is required. This flux has also been used for brazing in furnaces that have poor atmospheres, where a flux is required to achieve filler metal wetting.

It can be used on precious metals as well as all of the common engineering materials (copper, brass, mild steel and stainless steel, but not aluminium). JM special purpose fluxes are required when brazing aluminium bronze, certain grades of stainless steel, tungsten, molybdenum and tungsten carbide or where protracted heating is involved.

Conforms to: AWS FB3E, EN 1045: FH10

Working range: 600-850°C

Directions for Use

Easy-flo™ No. 25 Liquid Flux is concentrated and may be used in this form or diluted to a desired strength by adding water. It should be brushed onto the joint surfaces before assembly. Further flux should then be applied externally either side of the joint mouth. It is possible to apply this flux with automatic dispensing equipment.

It is good practice to mechanically clean and degrease the joint surface before applying flux. Heat slowly and evenly to the brazing temperature, without local overheating. If blackening of the flux occurs this is often a sign of insufficient flux, overheating or flux exhaustion.

Flux Residue Removal

The flux residues left after completion of the brazing operation are corrosive and should be removed. The residues of Easy-flo™ No. 25 Liquid Flux can easily be removed by soaking in hot water > 40°C for between 15 and 30 minutes. Any remaining residues can then be brushed off in running water.

Product Availability

1 litre containers

Easy-flo™, Silver-flo™ and Argo-braze™ are Johnson Matthey trademarks and are registered to JM in the EU and certain other countries.

Johnson Matthey Plc cannot anticipate all conditions under which this information and our products or the products of other manufacturers in combination with our products will be used. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is given in good faith, being based on the latest information available to Johnson Matthey Plc and is, to the best of Johnson Matthey Plc's knowledge and belief, accurate and reliable at the time of preparation. However, no representation, warranty or guarantee is made as to the accuracy or completeness of the information and Johnson Matthey Plc assumes no responsibility therefore and disclaims any liability for any loss, damage or injury howsoever arising (including in respect of any claim brought by any third party) incurred using this information. The product is supplied on the condition that the user accepts responsibility to satisfy himself as to the suitability and completeness of such information for his own particular use. Freedom from patent or any other proprietary rights of any third party must not be assumed. The text and images on this document are Copyright and property of Johnson Matthey.

This datasheet may only be reproduced as information, for use with or for resale of Johnson Matthey products. The JM logo®, Johnson Matthey name® and product names referred to in this document are trademarks of Johnson Matthey. Easy-flo® and Silver-flo® are registered to JM in the EU. Sil-fos™ is registered to JM in the UK and certain other countries but is marketed as Mattiphos™ in Germany and the USA.



Johnson Matthey

Metal Joining York Way, Royston, Hertfordshire, SG8 5HJ, UK

Telephone: +44 (0) 1763 253200

Fax: +44 (0) 1763 253168

email: mj@matthey.com

[www: jm-metaljoining.com](http://www.jm-metaljoining.com)